



Push-out collet, round, to DIN 6343, 173 E, Clamping \varnothing : 31 mm



Order data

Order number	329550 31
GTIN	4045197309792
Item class	34D

Description

Version:

Collets, **round profile in 1 mm increments. Please specify required clamping \varnothing with order.**

Standard:

DIN 6343

Accuracy:

Concentricity tolerances: D = 1 to 10 mm = 0.02 mm D = 10 to 30 mm = 0.03 mm D = 30 to 60 mm = 0.04 mm

Note:

Other diameters and profiles (e.g. square or hexagon) **on request!**

Profile \varnothing 1.0 – 8.0 mm smooth. From \varnothing 8.5 mm with transverse serrations.

Technical description

F	48 mm
A	50 mm
K	60 mm
Angle α	15 degrees
Clamping \varnothing	31 mm
Overall length L	94 mm
Type	173 E

Type of product

Collet