

# Three-jaw lathe chuck with recessed steel mount, DIN 702-4, External $\varnothing$ A: 80 mm



# **Order data**

Order number	310500 80
GTIN	4019208028316
Item class	36R

# **Description**

#### **Version:**

- · Manual chucks with gear scroll, centrically clamping.
- · Body made of cast iron or steel.
- · Gear scroll drop-forged, balanced, and hardened.
- · Flanks of scroll and of jaw serrations are ground.
- · High concentricity.

# **Application:**

For machine spindles with recessed centring mount or for mounting using a flange. Secured with screws from the rear. The flange blanks must always be fitted first to the machine and then to the chuck.

# Standard:

#### DIN 702-4.

## **Supplied with:**

1 set = 3 hard inside jaws, stepped on the outside and 1 set = 3 hard outside jaws, stepped on the inside.

1 clamping wrench and fastening screws or studs depending on the chuck.

## **Optional extras:**

For spare and additional jaws see No. 314000 – 315200. For swarf protection see No. 312800.

# Note:

DIN 702-4 satisfies the old standard DIN 6350-1.

For self-centring three-jaw lathe chucks see No. 313110 - 313140. Colour code for accessories: Röhm geared scroll chucks and jaws

Aperture E: 19 mm

Height without jaws H<sub>1</sub>: 39.5 mm Height with jaws H<sub>2</sub>: 53.5 mm

Centring Ø B: 56 mm Centring depth C: 3 mm Chuck key square K: 6 mm

# **Technical description**

External Ø A	80 mm
Height without jaws H₁	39.5 mm
Height with jaws H <sub>2</sub>	53.5 mm
Chuck key square K	6 mm
Centring Ø B	56 mm
Weight	1.3 kg
Centring depth C	3 mm
maximum speed	7000 rpm
Aperture E	19 mm
Standard	DIN 702-4
Material	Steel
Colour code for accessories	Röhm geared scroll chucks and jaws
Type of product	Gear scroll chucks

# **Accessories**

Scroll jaw set, 3 pieces, soft for chuck type 80 mm	314600 80
Inside jaw set, 3 pieces, hardened for chuck type 80	315000 80
Scroll jaw set 3-piece, soft for chuck type 80 mm	314620 80