

**Fabric adhesive tape stabilised, Width×length (mm× m): 50X50****Order data**

Order number	083605 50X50
GTIN	4042448141354
Item class	08M

Description**Version:**

tesa® 53799 exhibits very good adhesive strength even on rough substrates. It can be torn by hand easily and cleanly, is water-repellent, weather-resistant, resists heavy weights and is very supple. Thus it is ideal for a wide range of repair work and construction work, and also for packaging, bundling, bonding, etc.

Note:

The specified "best before" date for tesa® products is in relation to compliance with the specified storage guidelines.

Technical description

Thickness	0.31 mm
Colour	olive green
Length	50 m
Manufacturer's designation	53799
Width	50 mm

Storage temperature	15 - 35 °C
Adhesive	Natural rubber
Stretch capability	11 %
Backing material	Fabric
Storage humidity	50 - 70 %
temperature-resistant up to	110 °C
Tensile strength	7.7 N/mm
Liner present	no
Special features	supple
Special features	can be torn by hand
Special features	abrasion resistant
Fabric fineness	80 mesh
Type of adhesive tape	single-sided
Application	Joining
Application	Packing
Application	Binding
Application	Covering
Application	Bonding
Adhesive strength on steel	0.47 N/mm
Type of product	Adhesive tape