

Garant**Three-jaw lathe chuck with recessed steel mount, DIN 702-4, External Ø A: 200mm****Order data**

Order number

310600 200

GTIN

Item class

31R

Description**Version:**

- **Manual chucks with gear scroll, centrally clamping.**
- **Weight-reduced body of steel.**
- **Gear scroll drop-forged, balanced, and hardened.**
- **Flanks of scroll and of jaw serrations are ground.**
- **High concentricity.**

Application:

For machine spindles with recessed centring mount or for mounting using a flange. Secured with screws from the rear. The flange blanks must always be fitted first to the machine and then to the chuck.

Standard:**DIN 702-4.****Supplied with:**

1 clamping wrench and fastening screws or studs depending on the chuck.

Reversible jaws **with elliptical-bevelled teeth.**

Optional extras:

Spare and additional jaws see No. 314000 – 315200.

Swarf protection see No. 312800.

Note:

DIN 702-4 satisfies the old standard DIN 6350-1.

For self-centring three-jaw lathe chucks see No. 313120 – 313140.

Technical description

Weight	15.2 kg
External \varnothing A	200 mm
Chuck key square K	11 mm
Height without jaws H ₁	73.5 mm
maximum speed	3400 min ⁻¹
Centring depth C	4 mm
Aperture E	55 mm
Height with jaws H ₂	106 mm
Centring \varnothing B	160 mm
Standard	DIN 702-4
Material	Steel
Colour code for accessories	Röhm geared scroll chucks and jaws
Type of product	Gear scroll chucks

Accessories

Workpiece back-stop, base module Height h 15 mm	313036 15
Scroll jaw set, 3 pieces, soft for chuck type 200 mm	314600 200
Outside jaw set, 3 pieces, hardened for chuck type 200	315200 200
Workpiece backstop Height h 15 mm	313033 15
Base jaw set, 3 pieces, hardened for chuck type 200 mm	314000 200
Inside jaw set, 3 pieces, hardened for chuck type 200	315000 200
Top jaw set, 3 pieces, soft for chuck type 200 mm	314400 200