

**Arbor spacer ring, wide, Inner Ø×thickness b1: 40X2mm****Order data**

Order number	309930 40X2
GTIN	4045197307446
Item class	37D

**Description****Version:**

2.0 – 60 mm wide. Made of case-hardening steel, hardened. External Ø ground, flat surfaces lapped. Permissible variation in parallelism for the width is IT 3, referred to bore dia. d1. Tolerance of the ring width  $\pm 0.1$  mm.

**Technical description**

Thickness b <sub>1</sub>	2 mm
External Ø	55 mm
Internal Ø	40 mm
Version	wide
Standard	DIN 2084
Type of product	Arbor spacer ring