

Arbor spacer ring, wide, Inner Ø×thickness b1: 40X3mm**Order data**

| | |
|--------------|---------------|
| Order number | 309930 40X3 |
| GTIN | 4045197307453 |
| Item class | 37D |

Description**Version:**

2.0 – 60 mm wide. Made of case-hardening steel, hardened. External Ø ground, flat surfaces lapped. Permissible variation in parallelism for the width is IT 3, referred to bore dia. d1. Tolerance of the ring width ± 0.1 mm.

Technical description

| | |
|--------------------------|-------------------|
| Thickness b ₁ | 3 mm |
| External Ø | 55 mm |
| Internal Ø | 40 mm |
| Version | wide |
| Standard | DIN 2084 |
| Type of product | Arbor spacer ring |