

3M**Fabric adhesive tape UV-resistant, blue-grey, Width×length (mm× m): 48X23**

Order data

Order number	083615 48X23
GTIN	480115385184
Item class	08M

Description

Version:

Due to its supple structure and **UV resistance** the **3M™ 8979** is suitable for permanent and temporary applications **indoors and outdoors**. In addition it is **water-repellent** and thus can also be used for **sealing**.

Function:

IP20: No protection against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and no protection against water.

Note:

The specified "best before" date for 3M™ products is in relation to compliance with the specified storage guidelines.

Type of adhesive tape: single-sided

Adhesive: Natural rubber

Thickness: 0.31 mm

Technical description

Length	23 m
Manufacturer's designation	8979

Thickness	0.31 mm
Width	48 mm
Colour	blue-grey
Storage humidity	50 - 60 %
Liner present	no
Adhesive	Natural rubber
Type of adhesive tape	single-sided
"Best before" date	18 mo
Storage temperature	20 - 23 °C
temperature-resistant up to	93 °C
Stretch capability	19 %
Tensile strength	6.3 N/mm
Special features	UV-resistant
Special features	supple
Special features	abrasion resistant
Backing material	Fabric
Application	Insulating
Application	Sealing
Application	Covering
Application	Closing
Application	Binding
Adhesive strength on steel	0.212 N/mm
Product name attribute	blue-grey
Type of product	Adhesive tape