



ER collet, ER 40, Nominal clamping \varnothing d: 10mm



Order data

Order number	309040 10
GTIN	4045197151728
Item class	32Z

Description

Version:

Through hardened and ground. Polished.

Note:

The **collet clamping \varnothing range is always up to 1 mm less than nominal**, e.g. \varnothing 10 – 9 mm, **except for \varnothing 1, 1.5 and 2 (where it is only 0.5 mm)**.

Technical description

Nominal clamping \varnothing d	10 mm
Adapter	ER 40
Standard	ISO 15488-B
Concentricity	$\leq 10 \mu\text{m}$
Type	472 E
External \varnothing D	41 mm
Overall length L	46 mm
Type of product	Collet

