



Cordless angle grinder 18V, for 125 mm discs Ø, with battery, with soft start and restart inhibit, in a case



Order data

Order number	077140 M18CAG-125
GTIN	4002395263486
Item class	03L

Description

Version:

18 V / 5.0 Ah FUEL™ Milwaukee cordless angle grinder:

- **long-life brushless motor, spindle locking, quick adjustment of the safety guard.**
- **Integral FIXTEC quick-release system for changing discs without using tools.**

Note:

See from No. 073809 and No. 073840 for suitable replacement batteries and accessories.

Technical description

Manufacturer's designation	M18CAG125X-502X
Motor design	brushless EC motor
Battery capacity	5 Ah
Weight	2.5 kg
maximum speed	8500 min ⁻¹
Battery voltage	18 V
Soft start	yes
maximum vibration to EN	3.4 m/s ²
Dead man's circuit	no

Kick-back stop	no
Restart block	yes
maximum cutting depth	33 mm
Quick-release clamping nut	yes
maximum disc Ø	125 mm
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
suitable battery - supplier / battery type / voltage	Milwaukee type HB 18 V
Overload protection	yes
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	2
Packaging	Modular case (HD=Heavy Duty)
Power supply	Rechargeable battery-powered
Series	FUEL
Type of product	Angle grinder

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/077140-M18CAG-125>