

Garant
Face mill arbor vibration damped, BT 40 A = 300, Spigot Ø d1: 16mm

Order data

Order number	303051 16
GTIN	4045197821652
Item class	31A

Description
Version:

- **Cylindrical form.**
- **Taper shank, spigot, and all contact surfaces are ground at the collar.**
- **With RFID/Balluffchip bore.**
- **Larger collar contact face.**
- **Vibration damped version, arbor with vibration-damping core.**

Advantage:

Significantly lower tendency to vibrate. Considerable increase in feed rate.

Supplied with:

Cutter lock screw and drive dog.

Optional extras:

Special toggle spanner No. 309840.

Note:

Further sizes on request.

Technical description

Overhang dimension A	300 mm
External Ø D	38 mm
Milling mandrel length L ₄	17 mm
Spigot Ø d ₁	16 mm
Adapter	BT 40 A = 300
Standard	DIN 6357
Arbor standard	DIN 69893

Arbor standard	JIS B6339
Arbor standard	JIS B6339
Shape	A
Balance quality G at rotational speed	G 6.3 at 8,000 rpm
Concentricity	≤ 6 µm
Machining strategy	HPC
Vibration	damped
Type of product	Milling head arbor

Accessories

Pull stud 60°sealed suitable for steep tapers 40	308785 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Pull stud 45°sealed suitable for steep tapers 40	308765 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Toggle spanner for mandrel Ø 16 mm	309840 16
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40