

**Garant**
**Face mill arbor vibration damped, BT 50 A = 300, Spigot Ø d1: 16mm**

**Order data**

Order number	303055 16
GTIN	4045197821706
Item class	31A

**Description**
**Version:**

- **Cylindrical form.**
- **Taper shank, spigot, and all contact surfaces are ground at the collar.**
- **With RFID/Balluffchip bore.**
- **Larger collar contact face.**
- **Vibration damped version, arbor with vibration-damping core.**

**Advantage:**

Significantly lower tendency to vibrate. Considerable increase in feed rate.

**Supplied with:**

Cutter lock screw and drive dog.

**Optional extras:**

Special toggle spanner No. 309840.

**Note:**

Further sizes on request.

**Technical description**

External Ø D	38 mm
Milling mandrel length L <sub>4</sub>	17 mm
Overhang dimension A	300 mm
Spigot Ø d <sub>1</sub>	16 mm
Adapter	BT 50 A = 300
Standard	DIN 6357
Arbor standard	DIN 69882-3

Arbor standard	JIS B6339
Arbor standard	JIS B6339
Shape	A
Balance quality G at rotational speed	G 6.3 at 8,000 rpm
Concentricity	≤ 6 µm
Machining strategy	HPC
Vibration	damped
Type of product	Milling head arbor

---

## Accessories

Pull stud 90°sealed suitable for steep tapers 50	308790 50
Pull stud 90°sealed suitable for steep tapers 50	308795 50
Pull stud 60°sealed suitable for steep tapers 50	308785 50
Pull stud 45°sealed suitable for steep tapers 50	308765 50
Toggle spanner for mandrel Ø 16 mm	309840 16
Pull stud 45°sealed suitable for steep tapers 50	308760 50