

Garant
Face mill arbor vibration damped, BT 50 A = 400, Spigot \varnothing d1: 22mm

Order data

Order number	303056 22
GTIN	4045197821751
Item class	31A

Description
Version:

- **Cylindrical form.**
- **Taper shank, spigot, and all contact surfaces are ground at the collar.**
- **With RFID/Balluffchip bore.**
- **Larger collar contact face.**
- **Vibration damped version, arbor with vibration-damping core.**

Advantage:

Significantly lower tendency to vibrate. Considerable increase in feed rate.

Supplied with:

Cutter lock screw and drive dog.

Optional extras:

Special toggle spanner No. 309840.

Note:

Further sizes on request.

Technical description

External \varnothing D	48 mm
Spigot \varnothing d ₁	22 mm
Overhang dimension A	400 mm
Milling mandrel length L ₄	19 mm
Clamping \varnothing D ₁	22 mm
Adapter	BT 50 A = 400
Standard	DIN 6357

Arbor standard	DIN 69882-3
Arbor standard	JIS B6339
Arbor standard	JIS B6339
Shape	A
Balance quality G at rotational speed	G 6.3 at 8,000 rpm
Concentricity	≤ 6 μm
Machining strategy	HPC
Vibration	damped
Type of product	Milling head arbor