

Garant
Face mill arbor vibration-damped, conical, HSK-A 63 A = 200, Spigot Ø d1: 16 mm

Order data

Order number	306703 16
GTIN	4045197821775
Item class	31A

Description
Version:

- **Shank, spigot, and all contact surfaces are ground at the collar.**
- **With Balluffchip bore.**
- **Increased collar contact surface.**

Vibration damped version, arbor with vibration-damping core.

Advantage:

Significantly lower tendency to vibrate. Considerable increase in feed rate.

Supplied with:

Cutter lock screw and drive dog.

Optional extras:

Special coolant pipe wrench No. 309840, coolant pipe No. 309880.

Note:

Further sizes on request.

External Ø D: 50 mm

Ø D₂: 38 mm

Milling mandrel length L₄: 17 mm

Technical description

External Ø D	50 mm
Spigot Ø d ₁	16 mm
Ø D ₂	38 mm

Milling mandrel length L ₄	17 mm
Adapter	HSK-A 63 A = 200
Standard	DIN 6357
Arbor standard	DIN 69893
Arbor standard	DIN 69882-3
Arbor standard	ISO 12164-1
Shape	A
Balance quality G at rotational speed	G 6.3 at 8,000 rpm
Concentricity	≤ 6 μm
Machining strategy	HPC
Vibration	damped
Type of product	Milling head arbor

Accessories

Toggle spanner for mandrel Ø 16 mm	309840 16
------------------------------------	-----------