

**HAINBUCH****Twist-out ring for clamping heads, Clamping head (SK): 80****Order data**

|              |               |
|--------------|---------------|
| Order number | 329835 80     |
| GTIN         | 2050001922588 |
| Item class   | 33H           |

**Description****Suitable for :**

Clamping head for boring out No. 329916; 329926; 329936; 329946; 329976.

**Technical description**

|                 |                |
|-----------------|----------------|
| Arbor size      | 80 mm          |
| Type of product | Twist-out ring |

**Accessories**

|  |           |
|--|-----------|
| Clamping head with transverse and longitudinal serrations.<br>Clamping $\varnothing$ (1 mm increments) 51 mm | 329944 51 |
| Clamping head smooth Clamping $\varnothing$ (1 mm increments) 41 mm  | 329940 41 |

|   |           |
|---|-----------|
| Clamping head smooth Clamping Ø (1 mm increments) 26 mm                                       | 329940 26 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 61 mm | 329944 61 |
| Clamping head smooth Clamping Ø (1 mm increments) 55 mm                                       | 329940 55 |
| Clamping head soft Initial bore Ø 40 mm   | 329946 40 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 38 mm | 329944 38 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 15 mm | 329944 15 |
| Clamping head smooth Clamping Ø (1 mm increments) 13 mm                                       | 329940 13 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 27 mm | 329944 27 |
| Clamping head smooth Clamping Ø (1 mm increments) 72 mm                                       | 329940 72 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 21 mm | 329944 21 |
| Clamping head smooth Clamping Ø (1 mm increments) 60 mm                                       | 329940 60 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 47 mm | 329944 47 |
| Clamping head soft Initial bore Ø 60 mm   | 329946 60 |
| Clamping head smooth Clamping Ø (1 mm increments) 38 mm                                       | 329940 38 |
| Clamping head smooth Clamping Ø (1 mm increments) 34 mm                                       | 329940 34 |
| Clamping head smooth Clamping Ø (1 mm increments) 11 mm                                       | 329940 11 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 56 mm | 329944 56 |
| Clamping head smooth Clamping Ø (1 mm increments) 66 mm                                       | 329940 66 |
|   | 329940 68 |

|   |           |
|---|-----------|
| Clamping head smooth Clamping Ø (1 mm increments) 68 mm                                       |           |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 37 mm | 329944 37 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 80 mm | 329944 80 |
| Clamping head smooth Clamping Ø (1 mm increments) 39 mm                                       | 329940 39 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 50 mm | 329944 50 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 63 mm | 329944 63 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 73 mm | 329944 73 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 17 mm | 329944 17 |
| Clamping head smooth Clamping Ø (1 mm increments) 63 mm                                       | 329940 63 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 25 mm | 329944 25 |
| Clamping head smooth Clamping Ø (1 mm increments) 22 mm                                       | 329940 22 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 71 mm | 329944 71 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 48 mm | 329944 48 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 79 mm | 329944 79 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 31 mm | 329944 31 |
| Clamping head smooth Clamping Ø (1 mm increments) 10 mm                                       | 329940 10 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 22 mm | 329944 22 |
|   | 329940 28 |

|   |           |
|---|-----------|
| Clamping head smooth Clamping Ø (1 mm increments) 28 mm                                       |           |
| Clamping head smooth Clamping Ø (1 mm increments) 57 mm                                       | 329940 57 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 26 mm | 329944 26 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 75 mm | 329944 75 |
| Clamping head smooth Clamping Ø (1 mm increments) 36 mm                                       | 329940 36 |
| Clamping head smooth Clamping Ø (1 mm increments) 58 mm                                       | 329940 58 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 13 mm | 329944 13 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 44 mm | 329944 44 |
| Clamping head smooth Clamping Ø (1 mm increments) 37 mm                                       | 329940 37 |
| Clamping head smooth Clamping Ø (1 mm increments) 7 mm  | 329940 7  |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 65 mm | 329944 65 |
| Clamping head smooth Clamping Ø (1 mm increments) 23 mm                                       | 329940 23 |
| Clamping head smooth Clamping Ø (1 mm increments) 21 mm                                       | 329940 21 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 14 mm | 329944 14 |
| Clamping head smooth Clamping Ø (1 mm increments) 65 mm                                       | 329940 65 |
| Clamping head smooth Clamping Ø (1 mm increments) 52 mm                                       | 329940 52 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 66 mm | 329944 66 |
|   | 329944 60 |

Clamping head with transverse and longitudinal serrations.  
Clamping Ø (1 mm increments) 60 mm

Clamping head smooth Clamping Ø (1 mm increments) 71 mm

329940 71

Clamping head smooth Clamping Ø (1 mm increments) 76 mm

329940 76

Clamping head with transverse and longitudinal serrations.  
Clamping Ø (1 mm increments) 16 mm

329944 16

Clamping head smooth Clamping Ø (1 mm increments) 78 mm

329940 78

Clamping head with transverse and longitudinal serrations.  
Clamping Ø (1 mm increments) 55 mm

329944 55

Clamping head smooth Clamping Ø (1 mm increments) 35 mm

329940 35

Clamping head with transverse and longitudinal serrations.  
Clamping Ø (1 mm increments) 78 mm

329944 78

Clamping head with transverse and longitudinal serrations.  
Clamping Ø (1 mm increments) 29 mm

329944 29

Clamping head smooth Clamping Ø (1 mm increments) 77 mm

329940 77

Clamping head smooth Clamping Ø (1 mm increments) 5 mm

329940 5

Clamping head smooth Clamping Ø (1 mm increments) 48 mm

329940 48

Clamping head with transverse and longitudinal serrations.  
Clamping Ø (1 mm increments) 18 mm

329944 18

Clamping head smooth Clamping Ø (1 mm increments) 20 mm

329940 20

Clamping head smooth Clamping Ø (1 mm increments) 31 mm

329940 31

Clamping head with transverse and longitudinal serrations.  
Clamping Ø (1 mm increments) 34 mm

329944 34

Clamping head smooth Clamping Ø (1 mm increments) 59 mm

329940 59

329940 18

|   |           |
|---|-----------|
| Clamping head smooth Clamping Ø (1 mm increments) 18 mm                                       |           |
| Clamping head smooth Clamping Ø (1 mm increments) 9 mm  | 329940 9  |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 40 mm | 329944 40 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 30 mm | 329944 30 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 43 mm | 329944 43 |
| Clamping head smooth Clamping Ø (1 mm increments) 70 mm                                       | 329940 70 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 54 mm | 329944 54 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 11 mm | 329944 11 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 76 mm | 329944 76 |
| Clamping head smooth Clamping Ø (1 mm increments) 25 mm                                       | 329940 25 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 52 mm | 329944 52 |
| Clamping head smooth Clamping Ø (1 mm increments) 51 mm                                       | 329940 51 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 69 mm | 329944 69 |
| Clamping head smooth Clamping Ø (1 mm increments) 32 mm                                       | 329940 32 |
| Clamping head smooth Clamping Ø (1 mm increments) 62 mm                                       | 329940 62 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 53 mm | 329944 53 |
| Clamping head with transverse serrations. Clamping Ø (1 mm increments) 10 mm                  | 329942 10 |
|   | 329944 39 |

Clamping head with transverse and longitudinal serrations.  
Clamping Ø (1 mm increments) 39 mm

Clamping head smooth Clamping Ø (1 mm increments) 30 mm 329940 30

Clamping head with transverse and longitudinal serrations.  
Clamping Ø (1 mm increments) 42 mm 329944 42

Clamping head with transverse and longitudinal serrations.  
Clamping Ø (1 mm increments) 33 mm 329944 33

Clamping head with transverse serrations. Clamping Ø (1 mm increments) 9 mm 329942 9

Clamping head smooth Clamping Ø (1 mm increments) 42 mm 329940 42

Clamping head with transverse and longitudinal serrations.  
Clamping Ø (1 mm increments) 68 mm 329944 68

Clamping head with transverse and longitudinal serrations.  
Clamping Ø (1 mm increments) 32 mm 329944 32

Clamping head with transverse and longitudinal serrations.  
Clamping Ø (1 mm increments) 23 mm 329944 23

Clamping head smooth Clamping Ø (1 mm increments) 17 mm 329940 17

Clamping head smooth Clamping Ø (1 mm increments) 67 mm 329940 67

Clamping head smooth Clamping Ø (1 mm increments) 49 mm 329940 49

Clamping head with transverse and longitudinal serrations.  
Clamping Ø (1 mm increments) 77 mm 329944 77

Clamping head with transverse and longitudinal serrations.  
Clamping Ø (1 mm increments) 70 mm 329944 70

Clamping head soft Initial bore Ø 20 mm 329946 20

Clamping head smooth Clamping Ø (1 mm increments) 53 mm 329940 53

Clamping head smooth Clamping Ø (1 mm increments) 8 mm 329940 8

Clamping head smooth Clamping Ø (1 mm increments) 40 mm 329940 40

|   |           |
|---|-----------|
| Clamping head smooth Clamping Ø (1 mm increments) 50 mm                                       | 329940 50 |
| Clamping head smooth Clamping Ø (1 mm increments) 64 mm                                       | 329940 64 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 35 mm | 329944 35 |
| Clamping head smooth Clamping Ø (1 mm increments) 44 mm                                       | 329940 44 |
| Clamping head smooth Clamping Ø (1 mm increments) 56 mm                                       | 329940 56 |
| Clamping head smooth Clamping Ø (1 mm increments) 69 mm                                       | 329940 69 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 36 mm | 329944 36 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 57 mm | 329944 57 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 12 mm | 329944 12 |
| Clamping head smooth Clamping Ø (1 mm increments) 47 mm                                       | 329940 47 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 19 mm | 329944 19 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 59 mm | 329944 59 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 24 mm | 329944 24 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 72 mm | 329944 72 |
| Clamping head smooth Clamping Ø (1 mm increments) 75 mm                                       | 329940 75 |
| Clamping head smooth Clamping Ø (1 mm increments) 29 mm                                       | 329940 29 |
| Clamping head soft Initial bore Ø 8 mm  | 329946 8  |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 28 mm | 329944 28 |



|   |           |
|---|-----------|
| Clamping head smooth Clamping Ø (1 mm increments) 74 mm                                       | 329940 74 |
| Clamping head smooth Clamping Ø (1 mm increments) 43 mm                                       | 329940 43 |
| Clamping head smooth Clamping Ø (1 mm increments) 80 mm                                       | 329940 80 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 74 mm | 329944 74 |
| Clamping head smooth Clamping Ø (1 mm increments) 45 mm                                       | 329940 45 |
| Clamping head smooth Clamping Ø (1 mm increments) 14 mm                                       | 329940 14 |
| Clamping head with transverse serrations. Clamping Ø (1 mm increments) 8 mm                   | 329942 8  |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 45 mm | 329944 45 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 46 mm | 329944 46 |
| Clamping head smooth Clamping Ø (1 mm increments) 79 mm                                       | 329940 79 |
| Clamping head smooth Clamping Ø (1 mm increments) 46 mm                                       | 329940 46 |
| Clamping head smooth Clamping Ø (1 mm increments) 15 mm                                       | 329940 15 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 41 mm | 329944 41 |
| Clamping head with transverse and longitudinal serrations. Clamping Ø (1 mm increments) 20 mm | 329944 20 |
| Clamping head smooth Clamping Ø (1 mm increments) 12 mm                                       | 329940 12 |
| Clamping head smooth Clamping Ø (1 mm increments) 19 mm                                       | 329940 19 |
| Clamping head smooth Clamping Ø (1 mm increments) 54 mm                                       | 329940 54 |
|   | 329944 67 |

Clamping head with transverse and longitudinal serrations.  
Clamping Ø (1 mm increments) 67 mm

Clamping head smooth Clamping Ø (1 mm increments) 16 mm

329940 16

Clamping head with transverse and longitudinal serrations.  
Clamping Ø (1 mm increments) 62 mm

329944 62

Clamping head smooth Clamping Ø (1 mm increments) 6 mm

329940 6

Clamping head smooth Clamping Ø (1 mm increments) 24 mm

329940 24

Clamping head with transverse and longitudinal serrations.  
Clamping Ø (1 mm increments) 58 mm

329944 58

Clamping head with transverse and longitudinal serrations.  
Clamping Ø (1 mm increments) 64 mm

329944 64

Clamping head with transverse and longitudinal serrations.  
Clamping Ø (1 mm increments) 49 mm

329944 49

Clamping head smooth Clamping Ø (1 mm increments) 33 mm

329940 33

Clamping head smooth Clamping Ø (1 mm increments) 73 mm

329940 73

Clamping head smooth Clamping Ø (1 mm increments) 27 mm

329940 27

Clamping head smooth Clamping Ø (1 mm increments) 61 mm

329940 61