

**Stationary chuck MANOK, Clamping head (SK): 42****Order data**

Order number	329810 42
GTIN	2050001922472
Item class	33H

Description**Version:**

Stationary chuck of solid cast. High clamping force, precision and rigidity.

Application:

Versatile application, e.g. machining centres, measuring machines, pillar drills.

Supplied with:

Including 1 chuck key.

Note:

For suitable clamping heads see No.329910–329946.

Technical description

Width B	159 mm
Height H	124 mm
Weight	15 kg
Length L	214 mm
Arbor size	42
Repetition accuracy	0.01 mm
Head Ø	80 mm

Spacing of attachment holes	184 mm
Pitch circle Ø	120 mm
Width across flats	17 mm
maximum clamping force	80 kN
Clamping range	4 - 42 mm
Type of product	Vice