



**Clamping head smooth, SK 42, Clamping  $\varnothing$  (0.5 mm increments): 14,5mm**



## Order data

Order number	329910 14,5
GTIN	2050001073433
Item class	33H

## Description

### Version:

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify required clamping  $\varnothing$  with order.**

Smooth version for precision machining.

### Application:

Versatile application range: machining centres, measuring machines, and pallet clamping.

### Note:

**Clamping heads for special profiles to your individual requirements on request.**

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

## Technical description

Clamping $\varnothing$	14.5 mm
Clamping range	3 - 7.5 mm
Profile	round
Hardness	60 HR
Clamping face	smooth

Length L	42 mm
Version	shortened fittings
Adapter	SK 42
Type of product	Clamping head