

**Stationary chuck MANOK, Clamping head (SK): 65****Order data**

Order number	329810 65
GTIN	2050001922496
Item class	33H

**Description****Version:**

Stationary chuck of solid cast. High clamping force, precision and rigidity.

**Application:**

Versatile application, e.g. machining centres, measuring machines, pillar drills.

**Supplied with:**

Including 1 chuck key.

**Note:**

For suitable clamping heads see No.329910–329946.

**Technical description**

Length L	214 mm
Weight	13 kg
Height H	124 mm
Width B	159 mm
Arbor size	65
Head Ø	99.5 mm
Repetition accuracy	0.01 mm

Pitch circle Ø	120 mm
Width across flats	17 mm
maximum clamping force	105 kN
Spacing of attachment holes	184 mm
Clamping range	4 - 65 mm
Type of product	Vice