

**Stationary chuck MANOK, Clamping head (SK): 80****Order data**

Order number	329810 80
GTIN	2050001922502
Item class	33H

Description**Version:**

Stationary chuck of solid cast. High clamping force, precision and rigidity.

Application:

Versatile application, e.g. machining centres, measuring machines, pillar drills.

Supplied with:

Including 1 chuck key.

Note:

For suitable clamping heads see No.329910–329946.

Technical description

Length L	264 mm
Height H	140 mm
Width B	210 mm
Weight	23 kg
Arbor size	80
Repetition accuracy	0.01 mm
Spacing of attachment holes	236 mm

Pitch circle Ø	165 mm
maximum clamping force	115 kN
Width across flats	17 mm
Head Ø	115 mm
Clamping range	5 - 80 mm
Type of product	Vice