

Garant

Three-jaw lathe chuck steel short taper mount, DIN 702-3, Outer Ø A / taper: 250/6mm


Order data

Order number	310750 250/6
GTIN	4045197152169
Item class	31R

Description
Version:

- **Manual chucks with gear scroll, centrally clamping.**
- **Weight-reduced body of steel.**
- **Gear scroll drop-forged, balanced, and hardened.**
- **Flanks of scroll and of jaw serrations are ground.**
- **High concentricity.**

Application:

The chuck is always fitted to the spindle nose directly without an intermediate flange.

For spindle noses DIN 55027 **with studs and collar nuts.**

Standard:

DIN 702-3.

Supplied with:

1 clamping wrench and fastening screws or studs depending on the chuck.

1 set reversible jaws **with elliptical–bevelled serrations.**

Optional extras:

For spare and additional jaws see No. 314000 – 315200. **For swarf protection** see No. 312800.

Note:

For self-centring three-jaw lathe chucks see No. 313120 – 313140.

DIN 702-3 satisfies the old standard DIN 55029.

Colour code for accessories: Röhm geared scroll chucks and jaws

Aperture E: 76 mm

Height without jaws H₁: 83 mm

Height with jaws H₂: 124 mm

Number of studs: 4

Size of studs: M12

Chuck key square K: 12 mm

Technical description

Aperture E	76 mm
Weight	28 kg
maximum speed	2700 min ⁻¹
Taper size	6
Size of studs	M12
Number of studs	4
Height with jaws H ₂	124 mm
External Ø A	250 mm
Height without jaws H ₁	83 mm
Chuck key square K	12 mm
Standard	DIN 702-3
Colour code for accessories	Röhm geared scroll chucks and jaws
Type of product	Gear scroll chucks

Accessories

Outside jaw set, 3 pieces, hardened for chuck type 250	315200 250
Workpiece backstop Height h 15 mm	313033 15
Scroll jaw set 3-piece, soft for chuck type 250 mm	314620 250
Base jaw set, 3 pieces, hardened for chuck type 250 mm	314000 250
Top jaw set, 3 pieces, soft for chuck type 250 mm	314400 250
Inside jaw set, 3 pieces, hardened for chuck type 250	315000 250

Scroll jaw set, 3 pieces, soft for chuck type 250 mm	314600 250
Workpiece back-stop, base module Height h 15 mm	313036 15
Base jaw set 3-piece, hardened for chuck type 250 mm	314020 250
Top jaw set 3-piece, soft for chuck type 250 mm	314420 250