

**Angle grinder Classic, Type: 72210500****Order data**

Order number	077151 72210500
GTIN	4014586851242
Item class	03F

Description**Version:**

- **FEIN high power motor with enormous traction power for high removal rates.**
- **Automatic restart inhibit after power supply interruption.**
- **Rear handle can be turned to 4 positions.**
- **Non-wearing EBS electrical braking system stops the machine in less than 3 seconds.**
- **FEIN quick-release clamping system QuickIN for quick easy and reliable disc changes without using tools.**

Function:

IP20: No protection against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and no protection against water.

Supplied with:

Supplied with protective hood, additional handle, clamping set.

Manufacturer's designation: WSB 20-180

Power consumption: 2000 W

maximum speed: 8,500 min⁻¹

maximum disc \varnothing : 180 mm

maximum cutting depth: 48 mm

Weight: 4.8 kg

Technical description

Power consumption	2000 W
Special features	QuickIN

Manufacturer's designation	WSB 20-180
maximum speed	8,500 min ⁻¹
maximum disc Ø	180 mm
maximum vibration to EN	6 m/s ²
Weight	4.8 kg
maximum cutting depth	48 mm
Power supply	Mains operated
Type of product	Angle grinder