

Garant
Side lock arbor, HSK-A 100 short, Clamping range \varnothing D1: 32mm

Order data

Order number	304390 32
GTIN	4045197289254
Item class	31A

Description
Version:

- With RFID/Balluffchip bore.
- HSK mating faces machined.

GARANT: All shanks hard turned (for smooth cutting action!).

Application:

For clamping tools with Weldon shank to DIN 1835 Form B and DIN 6535 Form HB.

Optional extras:

Coolant pipe No. 309880, coolant pipe wrench No. 309890

Note:

HSK 40 and 50, Form A and E available ex works by the manufacturer.

Technical description

Spare clamping screw No. 30 9900	32
Clamping \varnothing D ₁	32 mm
Overhang dimension A	100 mm
External \varnothing D	72 mm
Adapter	HSK-A 100 short
Arbor standard	DIN 69893
Arbor standard	DIN 69882-4

Arbor standard	ISO 12164-1
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HPC
Machining strategy	HSC
Type of product	Side lock arbor

Accessories

Socket wrench for coolant tubes for HSK 32	309890 32
Spare clamping screw for chucks with clamping \varnothing D1 32 mm	309900 32
HSK coolant tube for HSK 32	309880 32