

Garant
Side lock arbor, HSK-A 63 A = 160, Clamping range \varnothing D1: 25mm

Order data

| | |
|--------------|---------------|
| Order number | 304335 25 |
| GTIN | 4045197289148 |
| Item class | 31A |

Description
Version:

- With RFID/Balluffchip bore.
- HSK mating faces machined.

GARANT: All shanks hard turned (for smooth cutting action!).

Application:

For clamping tools with Weldon shank to DIN 1835 Form B and DIN 6535 Form HB.

Optional extras:

Coolant pipe No. 309880, coolant pipe wrench No. 309890

Note:

HSK 40 and 50, Form A and E available ex works by the manufacturer.

Technical description

| | |
|---------------------------------------|------------------|
| Overhang dimension A | 160 mm |
| Spare clamping screw No. 30 9900 | 25 |
| Clamping \varnothing D ₁ | 25 mm |
| External \varnothing D | 65 mm |
| Adapter | HSK-A 63 A = 160 |
| Arbor standard | DIN 69893 |
| Arbor standard | DIN 69882-4 |

| | |
|---------------------------------------|---------------------|
| Arbor standard | ISO 12164-1 |
| Shape | A |
| Balance quality G at rotational speed | G 2.5 at 25,000 rpm |
| Concentricity | ≤ 3 µm |
| Machining strategy | HSC |
| Machining strategy | HPC |
| Type of product | Side lock arbor |

Accessories

| | |
|--|-----------|
| Spare clamping screw for chucks with clamping Ø D1 25 mm | 309900 25 |
| HSK coolant tube for HSK 25 | 309880 25 |
| Socket wrench for coolant tubes for HSK 25 | 309890 25 |