

**Garant**
**Side lock arbor, HSK-A 63 A = 160, Clamping range  $\varnothing$  D1: 32mm**

**Order data**

Order number	304335 32
GTIN	4045197289155
Item class	31A

**Description**
**Version:**

- With RFID/Balluffchip bore.
- HSK mating faces machined.

**GARANT:** All shanks hard turned (for smooth cutting action!).

**Application:**

For clamping tools with Weldon shank to DIN 1835 Form B and DIN 6535 Form HB.

**Optional extras:**

Coolant pipe No. 309880, coolant pipe wrench No. 309890

**Note:**

HSK 40 and 50, Form A and E available ex works by the manufacturer.

**Technical description**

Overhang dimension A	160 mm
Spare clamping screw No. 30 9900	32
Clamping $\varnothing$ D <sub>1</sub>	32 mm
External $\varnothing$ D	72 mm
Adapter	HSK-A 63 A = 160
Arbor standard	DIN 69893
Arbor standard	DIN 69882-4

Arbor standard	ISO 12164-1
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HSC
Machining strategy	HPC
Type of product	Side lock arbor

---

## Accessories

HSK coolant tube for HSK 32	309880 32
Socket wrench for coolant tubes for HSK 32	309890 32
Spare clamping screw for chucks with clamping $\varnothing$ D1 32 mm	309900 32