

Garant

**Side lock arbor with cooling channel bore, HSK-A 63 A = 120, Clamping range
Ø D1: 6mm**


Order data

Order number	304328 6
GTIN	4045197468178
Item class	31A

Description
Version:

- **With RFID/Balluffchip bore.**
- **HSK mating faces machined.**

GARANT: All shanks hard turned (for smooth cutting action!).

With coolant supply holes that can be plugged.

Application:

For clamping tools with Weldon shank to DIN 1835 Form B and DIN 6535 Form HB.

Optional extras:

Coolant pipe No. 309880, coolant pipe wrench No. 309890

Note:

HSK 40 and 50, Form A and E available ex works by the manufacturer.

Technical description

Spare clamping screw No. 30 9900	6
Overhang dimension A	120 mm
Clamping Ø D ₁	6 mm
External Ø D	25 mm
Adapter	HSK-A 63 A = 120

Arbor standard	DIN 69893
Arbor standard	DIN 69882-4
Arbor standard	ISO 12164-1
Shape	A
Cooling channel bore	pluggable
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HPC
Machining strategy	HSC
Type of product	Side lock arbor

Accessories

Spare clamping screw for chucks with clamping \varnothing D1 6 mm	309900 6
---	----------