

**Garant**
**Side lock arbor, HSK-A 100 A = 160, Clamping range  $\varnothing$  D<sub>1</sub>: 10mm**


## Order data

Order number	304410 10
GTIN	4045197289384
Item class	31A

## Description

### Version:

- With RFID/Balluffchip bore.
- HSK mating faces machined.

**GARANT:** All shanks hard turned (for smooth cutting action!).

### Application:

For clamping tools with Weldon shank to DIN 1835 Form B and DIN 6535 Form HB.

### Optional extras:

Coolant pipe No. 309880, coolant pipe wrench No. 309890

### Note:

HSK 40 and 50, Form A and E available ex works by the manufacturer.

## Technical description

Spare clamping screw No. 30 9900	10
Clamping $\varnothing$ D <sub>1</sub>	10 mm
Overhang dimension A	160 mm
External $\varnothing$ D	35 mm
Adapter	HSK-A 100 A = 160
Arbor standard	DIN 69893
Arbor standard	DIN 69882-4

Arbor standard	ISO 12164-1
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HPC
Machining strategy	HSC
Type of product	Side lock arbor

---

## Accessories

Spare clamping screw for chucks with clamping $\varnothing$ D1 10 mm	309900 10
--	-----------