



Angle grinder, Type: AGVM26-230



Order data

Order number	077161 AGVM26-230
GTIN	4002395234271
Item class	03M

Description

Version:

Powerful 230 mm angle grinder:

- **Dust-proof PROtector motor with smooth start-up and inrush current limitation.**
- **Safeguard against accidental restart.**
- **Vibration-damped adjustable handle.**
- **Spindle locking pin.**

2600 W motor. With B-Guard anti-kickback **safety shut-off**, **FIXTEC** clamping nut and auto-balancer.

Supplied with:

Supplied with protective hood, additional handle. FIXTEC quick-clamping nut.

Technical description

maximum cutting depth	68 mm
Soft start	yes
maximum vibration to EN	2.5 m/s ²
Weight	5.8 kg
Power consumption	2600 W
maximum disc Ø	230 mm
Manufacturer's designation	AGVM26-230GEXProTector
Special features	FIXTEC

Special features	Autobalancer
Special features	Dead man's switch
Special features	adjustable handle
Restart block	yes
Power supply	Mains operated
maximum speed	6600 min ⁻¹
Type of product	Angle grinder

Accessories

Clamping nut M14 Type FIXTEC	073930 FIXTEC
Clamping nut M14 Type NUT	073930 NUT