

HAINBUCH
Clamping head with transverse serrations., SK 42, Clamping \varnothing (0.5 mm increments): 9 mm


Order data

Order number	329912 9
GTIN	2050001071392
Item class	33H

Description

Version:

With transverse serrations for raw material, small \varnothing .

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify required clamping \varnothing with order.**

Application:

Versatile application range: machining centres, measuring machines, and pallet clamping.

Note:

Clamping heads for special profiles to your individual requirements on request.

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

Technical description

Clamping \varnothing	9 mm
Clamping face	Transverse serrations
Clamping range	8 - 10.5 mm
Hardness	60 HR

Profile	round
Length L	47 mm
Adapter	SK 42
Type of product	Clamping head