



Clamping head smooth, SK 42, Clamping \varnothing (0.5 mm increments): 30,5mm



Order data

Order number	329910 30,5
GTIN	2050001073594
Item class	33H

Description

Version:

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify required clamping \varnothing with order.**

Smooth version for precision machining.

Application:

Versatile application range: machining centres, measuring machines, and pallet clamping.

Note:

Clamping heads for special profiles to your individual requirements on request.

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

Technical description

Clamping \varnothing	30.5 mm
Hardness	60 HR
Clamping face	smooth
Profile	round
Clamping range	3 - 7.5 mm

Length L	42 mm
Version	shortened fittings
Adapter	SK 42
Type of product	Clamping head