

HELICOIL® Plus
made by BOLLHOFF
Thread repair set DIN 8140, Thread M (×pitch): M2,5

Order data

Order number	082800 M2,5
GTIN	4250361200014
Item class	04D

Description
Version:

High-strength HeliCoil®plus threaded inserts of stainless steel with **high wear-resistance**, **low thread friction** in close tolerances, **high surface quality** as well as **corrosion** and **heat resistance**. The flexible construction allows an even distribution of load and tension forces and thus allows creation of very high quality **permanent** screw connections with **ideal force transfer** for all **working loads** (static, dynamic). Uncomplicated quick insertion, resulting in an internal thread that can be used from both ends.

Complete repair set, for one each metric thread size in a plastic case.

Application:

For economic **repair of damaged** or **worn threads** and as a design element for **thread reinforcement** in materials which have low shear strength (e.g. aluminium, aluminium-magnesium alloys).

Supplied with:

- 1 HSS hand tap
- 1 insertion spindle.
- 1 plastic case L×W×H 180×165×45 mm (up to size M8) 245×225×50 mm (size M10 and above).
- 20 each (up to size M6) or 10 each (size M8 and above) stainless steel thread inserts for through bolts in each length (1×D / 1.5×D / 2×D).

1 drill.

1 tang breaker.

Note:

For TiCN coated HSS-E-PM machine taps see No. 133550 and No. 138200.

- **For suitable thread gauges for thread checking see No. 486000ff.**
- **Self-locking inserts, inserts with other dimensions and UNC/UNF thread inserts are available on request.**

Technical description

Thread M	M2.5
Tapping hole Ø	2.6 mm
Number of thread inserts	60
Type of product	Thread repair

Accessories

Spare hand tap 6H Thread M (xpitch) M2,5	082805 M2,5
--	-------------