



Clamping head with transverse and longitudinal serrations., SK 42, Clamping Ø (0.5 mm increments): 21,5mm



Order data

Order number	329914 21,5
GTIN	2050001073846
Item class	33H

Description

Version:

With transverse and longitudinal serrations for raw material.

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify required clamping Ø with order.**

Application:

Versatile application range, machining centres, measuring machines or pallet clamping.

Note:

Clamping heads for special profiles to your individual requirements on request.

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

Technical description

Clamping Ø	21.5 mm
Profile	round
Clamping range	11 - 42 mm
Hardness	60 HR

Clamping face	Transverse and longitudinal serrations
Length L	47 mm
Adapter	SK 42
Type of product	Clamping head