



## Clamping head smooth, SK 42, Clamping $\varnothing$ (0.5 mm increments): 28mm



### Order data

Order number	329910 28
GTIN	2050001071231
Item class	33H

### Description

#### Version:

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify required clamping  $\varnothing$  with order.**

Smooth version for precision machining.

#### Application:

Versatile application range: machining centres, measuring machines, and pallet clamping.

#### Note:

**Clamping heads for special profiles to your individual requirements on request.**

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

### Technical description

Clamping $\varnothing$	28 mm
Profile	round
Clamping range	3 - 7.5 mm
Hardness	60 HR
Clamping face	smooth

Length L	42 mm
Version	shortened fittings
Adapter	SK 42
Type of product	Clamping head