



## Clamping head with transverse and longitudinal serrations., SK 42, Clamping Ø (0.5 mm increments): 26,5mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 329914 26,5   |
| GTIN         | 2050001073891 |
| Item class   | 33H           |

### Description

#### Version:

With transverse and longitudinal serrations for raw material.

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify required clamping Ø with order.**

#### Application:

Versatile application range, machining centres, measuring machines or pallet clamping.

#### Note:

**Clamping heads for special profiles to your individual requirements on request.**

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

### Technical description

|                |            |
|----------------|------------|
| Clamping Ø     | 26.5 mm    |
| Clamping range | 11 - 42 mm |
| Profile        | round      |
| Hardness       | 60 HR      |

|                 |  |
|-----------------|--|
| Clamping face   | Transverse and longitudinal serrations |
| Length L        | 47 mm                                  |
| Adapter         | SK 42                                  |
| Type of product | Clamping head                          |