



## Clamping head with transverse and longitudinal serrations., SK 42, Clamping Ø (0.5 mm increments): 19mm



### Order data

Order number	329914 19
GTIN	2050001071491
Item class	33H

### Description

#### Version:

With transverse and longitudinal serrations for raw material.

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify required clamping Ø with order.**

#### Application:

Versatile application range, machining centres, measuring machines or pallet clamping.

#### Note:

**Clamping heads for special profiles to your individual requirements on request.**

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

### Technical description

Clamping Ø	19 mm
Clamping range	11 - 42 mm
Hardness	60 HR
Profile	round

Clamping face	Transverse and longitudinal serrations
Length L	47 mm
Adapter	SK 42
Type of product	Clamping head