



Angle grinder, Type: AGV24-230



Order data

Order number	077161 AGV24-230
GTIN	4002395234226
Item class	03M

Description

Version:

Powerful 230 mm angle grinder:

- **Dust-proof PROtector motor with smooth start-up and inrush current limitation.**
- **Safeguard against accidental restart.**
- **Vibration-damped adjustable handle.**
- **Spindle locking pin.**

Casing reduces the occurrence of vibration by up to 70%.

Supplied with:

Supplied with protective hood, additional handle.

Technical description

maximum disc Ø	230 mm
Restart block	yes
maximum cutting depth	68 mm
Manufacturer's designation	AGV24-230GProTector
maximum vibration to EN	2.7 m/s ²
Weight	5.5 kg
Special features	Autobalancer
Power consumption	2400 W

Soft start	yes
Power supply	Mains operated
maximum speed	6600 min ⁻¹
Type of product	Angle grinder

Accessories

Clamping nut M14 Type FIXTEC	073930 FIXTEC
Clamping nut M14 Type NUT	073930 NUT