



## Angle grinder Classic, Type: 72210800



### Order data

Order number	077151 72210800
GTIN	4014586851273
Item class	03F

### Description

#### Version:

- **FEIN high power motor with enormous traction power for high removal rates.**
- **Automatic restart inhibit after power supply interruption.**
- **Rear handle can be turned to 4 positions.**
- **Angle grinder with M14 clamping spindle (e. g. for use with cup brushes).**
- **Without QuickIN or EBS braking system.**

#### Function:

IP20: No protection against penetration by foreign bodies with  $\varnothing < 12$  mm, however touching should be avoided, and no protection against water.

#### Supplied with:

Supplied with protective hood, additional handle, clamping set.

Manufacturer's designation: WSG 20-230

Power consumption: 2000 W

maximum speed: 6,600 min<sup>-1</sup>

maximum disc  $\varnothing$ : 230 mm

maximum cutting depth: 66 mm

Weight: 4.5 kg

### Technical description

Manufacturer's designation	WSG 20-230
maximum vibration to EN	6 m/s <sup>2</sup>

maximum disc Ø	230 mm
maximum cutting depth	66 mm
Weight	4.5 kg
Power consumption	2000 W
maximum speed	6,600 min <sup>-1</sup>
Special features	M14
Power supply	Mains operated
Type of product	Angle grinder