



Angle grinder, Type: AGV15-125



Order data

Order number	077141 AGV15-125
GTIN	4002395239641
Item class	03M

Description

Version:

Milwaukee angle grinder with smooth start-up, **restart inhibit** and overload protection. 1550 W / 125 mm angle grinder with **constant-speed electronics**, anti-vibration handle, anti-kickback function for very high user protection, **FIXTEC** disc change without using tools.

Supplied with:

Additional handle, guard cover, 4 m power cable.

Technical description

maximum cutting depth	33 mm
maximum disc Ø	125 mm
maximum vibration to EN	4.7 m/s ²
Soft start	yes
Restart block	yes
Kick-back stop	yes
Manufacturer's designation	AGV15-125XCProTector
Power consumption	1550 W
Weight	2.6 kg
Power supply	Mains operated

maximum speed	11000 min ⁻¹
Type of product	Angle grinder

Accessories

Clamping nut M14 Type FIXTEC	073930 FIXTEC
Clamping nut M14 Type NUT	073930 NUT
Detachable protective guard for AGV15-125 Type GUARD-125	077142 GUARD-125