AEG

Straight die grinder, Type: GSL600E

Order data

Order number	077271 GSL600E
GTIN	4002395192946
Item class	07A

Description

Version:
Universal straight die grinder with electronic speed control.
- **Extra long grinding spindle and slender thermally insulated gearbox neck for working where access is difficult.**
- **Robust metal gearbox with double bearing. 4 m power cable.**

Supplied with:
Includes 6 mm ∅ collet, tightening spanner AF 15/17.
Note:
See No. 540200 ff for suitable burrs.
See No. 550600 ff for suitable grinding points.
See No. 551850 ff for suitable polishing points.

Technical description

Power consumption	600 W
maximum vibration to EN	3 m/s^2
Weight	1.9 kg
electronic speed pre-selection	yes
Manufacturer's designation	GSL600E
Speed range	10000 - 29000 min^{-1}
maximum collet ∅	6 mm

Power supply	Mains operated
Type of product	Straight die grinder

Accessories

Collet for straight die grinder No. 077271 Collet ∅ 6 mm	077270 6
Collet for straight die grinder No. 077271 Collet ∅ 8 mm	077270 8