

ER collet chuck set, HSK-A 63, for ER collet size: 32



Order data

Order number	305450 32
GTIN	4045197307934
Item class	37D

Description

Advantage:

Longer working life due to system run-out $\leq 10 \mu\text{m}$.

- **Optimum process reliability due to high clamping force.**
- **Better surface quality (quality, tighter production tolerances).**
- **Lower production costs.**

Supplied with:

ER chuck (**with nut**) No. 305390, including a plastic case. ER lock wrench No. 309680 – 32, ER collet No. 308981

ER 32 (470 E): D = 4, 6, 8, 10, 12, 14, 16, 18 and 20 mm.

Technical description

for ER collets	32
Adapter	HSK-A 63
Type of product	Collet chuck

Accessories

ER chuck key for ER collet chuck 32	309680 32
ER collet Nominal clamping Ø d 18 mm	309000 18
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 6 mm	309432 6
ER collet Nominal clamping Ø d 11 mm	309000 11
ER collet Nominal clamping Ø d 17 mm	309000 17
ER collet Nominal clamping Ø d 13 mm	309000 13
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 12 mm	309432 12
ER collet Nominal clamping Ø d 16 mm	309000 16
ER collet Nominal clamping Ø d 8 mm	309000 8
ER collet Nominal clamping Ø d 6 mm	309000 6
ER collet Nominal clamping Ø d 10 mm	309000 10
ER collet Nominal clamping Ø d 19 mm	309000 19
ER collet Nominal clamping Ø d 20 mm	309000 20
ER collet Nominal clamping Ø d 9 mm	309000 9
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 4,5 mm	309432 4,5
ER collet Nominal clamping Ø d 7 mm	309000 7
ER collet Nominal clamping Ø d 15 mm	309000 15
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 10 mm	309432 10
ER collet Nominal clamping Ø d 3 mm	309000 3
ER collet Nominal clamping Ø d 5 mm	309000 5
ER collet set 18 pieces 3–20 mm	309280
ER collet Nominal clamping Ø d 12 mm	309000 12
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 8 mm	309432 8
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 11 mm	309432 11

ER collet Nominal clamping Ø d 14 mm	309000 14
ER collet Nominal clamping Ø d 4 mm	309000 4
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 9 mm	309432 9
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 7 mm	309432 7
ER collet chuck for ER collet size 32	305390 32