

ER collet chuck set, HSK-A 63, for ER collet size: 16



Order data

Order number	305450 16
GTIN	4045197307941
Item class	37D

Description

Advantage:

Longer working life due to system run-out $\leq 10 \mu\text{m}$.

- **Optimum process reliability due to high clamping force.**
- **Better surface quality (quality, tighter production tolerances).**
- **Lower production costs.**

Supplied with:

ER chuck (**with nut**) No. 305390, including a plastic case. ER lock wrench No. 613300 size 25, ER collets No. 308901

ER 16 (426 E): D = 2, 3, 4, 5, 6, 7, 8, 9 and 10 mm.

Technical description

for ER collets	16
Adapter	HSK-A 63
Type of product	Collet chuck

Accessories

ER collet Nominal clamping Ø d 1 mm	308920 1
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 4,5 mm	309425 4,5
Single open ended spanner Width across flats 25 mm	613300 25
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 3,5 mm	309425 3,5
ER collet Nominal clamping Ø d 4 mm	308920 4
ER collet Nominal clamping Ø d 7 mm	308920 7
ER collet Nominal clamping Ø d 10 mm	308920 10
ER collet Nominal clamping Ø d 5 mm	308920 5
ER collet Nominal clamping Ø d 6 mm	308920 6
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 6 mm	309425 6
ER collet set 10 pieces 1–10 mm	309160
ER collet Nominal clamping Ø d 2 mm	308920 2
ER collet Nominal clamping Ø d 9 mm	308920 9
ER collet Nominal clamping Ø d 8 mm	308920 8
ER collet Nominal clamping Ø d 3 mm	308920 3
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 2,8 mm	309425 2,8
ER collet chuck for ER collet size 16	305390 16