



Clamping head soft, SK 42, Initial bore Ø: 30mm



Order data

Order number	329916 30
GTIN	2050001922618
Item class	33H

Description

Version:

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify required clamping Ø with order.**

Soft (reduced hardness of 40 HRC in the bore) for boring out.

Application:

Versatile application range: machining centres, measuring machines, and pallet clamping.

Note:

Clamping heads for special profiles to your individual requirements on request.

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

Technical description

Initial bore Ø	30 mm
Profile	round
Length L	47 mm
Adapter	SK 42
Type of product	Clamping head

