



Angle grinder Deadman, Type: AGVM26-230



Order data

Order number	077162 AGVM26-230
GTIN	4002395234394
Item class	03M

Description

Version:

Powerful 230 mm angle grinder:

- **Dust-proof PROtector motor with smooth start-up and inrush current limitation.**
- **Safeguard against accidental restart.**
- **Vibration-damped adjustable additional handle.**
- **Spindle locking pin.**

Version with dead-man's switch, which switches the machine off immediately the trigger is released. **2600 W** motor. With B-Guard anti-kickback **safety clutch** and **FIXTEC** clamping nut.

Supplied with:

Supplied with protective hood, additional handle. FIXTEC quick-clamping nut.

Technical description

Manufacturer's designation	AGVM26-230GEXProTector
maximum disc Ø	230 mm
maximum cutting depth	68 mm
maximum vibration to EN	2.5 m/s ²
Power consumption	2600 W
Soft start	yes
Restart block	yes
Dead man's circuit	yes

Weight	5.8 kg
Power supply	Mains operated
maximum speed	6600 min ⁻¹
Special features	Autobalancer
Special features	FIXTEC
Special features	Dead man's switch
Special features	adjustable handle
Type of product	Angle grinder

Accessories

Clamping nut M14 Type NUT	073930 NUT
Clamping nut M14 Type FIXTEC	073930 FIXTEC