



Angle grinder Classic, Type: 72211100



Order data

Order number	077151 72211100
GTIN	4014586853123
Item class	03F

Description

Version:

- **FEIN high power motor with enormous traction power for high removal rates.**
- **Automatic restart inhibit after power supply interruption.**
- **Rear handle can be turned to 4 positions.**
- **Non-wearing EBS electrical braking system stops the machine in less than 3 seconds.**
- **FEIN quick-release clamping system QuickIN for quick easy and reliable disc changes without using tools.**

Function:

IP20: No protection against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and no protection against water.

Supplied with:

Supplied with protective hood, additional handle, clamping set.

Manufacturer's designation: WSB 25-230X

Power consumption: 2500 W

maximum speed: 6,600 min⁻¹

maximum disc \varnothing : 230 mm

maximum cutting depth: 66 mm

Weight: 5.4 kg

Technical description

Weight	5.4 kg
Power consumption	2500 W

maximum cutting depth	66 mm
maximum vibration to EN	6 m/s ²
Special features	QuickIN
maximum speed	6,600 min ⁻¹
Manufacturer's designation	WSB 25-230X
maximum disc Ø	230 mm
Power supply	Mains operated
Type of product	Angle grinder