

HELICOIL® Plus
made by **BOLLHOFF****Spare hand tap 6H, Thread M (×pitch): M12****Order data**

Order number	082805 M12
GTIN	2050000000904
Item class	04D

Description**Version:**

High-strength HeliCoil®plus thread inserts for through bolts, of **stainless steel with high wear-resistance, low thread friction** in close tolerances, **high surface quality** as well as **corrosion** and **heat resistance**. The flexible construction allows an even distribution of load and tension forces and thus allows creation of very high quality **permanent** screw connections with **ideal force transfer** for all **working loads** (static, dynamic). Uncomplicated quick insertion, resulting in an internal thread that can be used from both ends.

HSS one-pass hand tap for through holes.

Application:

For economic **repair of damaged** or **worn threads** and as a design element for **thread reinforcement** in materials which have low shear strength (e.g. aluminium, aluminium-magnesium alloys).

Note:

For TiCN coated HSS-E-PM machine taps see No. 133550 and No. 138200.

For TiCN coated HSS-E-PM machine taps see No. 133550 and No. 138200.

Technical description

Thread M	M12
Tapping hole Ø	12.5 mm
Number of threaded inserts No. 082800	30
Type of product	Tap

