

**Clamping head smooth, SK 52, Clamping \varnothing (0.5 mm increments): 22,5mm****Order data**

Order number	329920 22,5
GTIN	2050001074232
Item class	33H

Description**Version:**

Smooth version for precision machining.

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify required clamping \varnothing with order.**

Application:

Versatile application range, machining centres, measuring machines or pallet clamping.

Note:

Clamping heads for special profiles to your individual requirements on request.

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

Technical description

Clamping \varnothing	22.5 mm
Profile	round
Hardness	60 HR
Clamping range	3 - 7.5 mm
Clamping face	smooth

Length L	46 mm
Version	shortened fittings
Adapter	SK 52
Type of product	Clamping head