



Angle grinder, Type: AGV17-125



Order data

Order number	077141 AGV17-125
GTIN	4002395243983
Item class	03M

Description

Version:

Milwaukee angle grinder with smooth start-up, **restart inhibit** and overload protection. 1750 W / 125 mm angle grinder with **electronic speed control**, anti-kickback function and soft start. **Anti-vibration handle**, disc change without using tools. **FIXTEC** clamping nut.

Supplied with:

Additional handle, guard cover, 4 m power cable.

Technical description

Soft start	yes
Restart block	yes
maximum vibration to EN	9.5 m/s ²
maximum cutting depth	33 mm
Power consumption	1750 W
Weight	2.8 kg
maximum disc Ø	125 mm
Kick-back stop	yes
Manufacturer's designation	AGV17-125XProTector
Power supply	Mains operated

maximum speed	2600 - 11000 min ⁻¹
Type of product	Angle grinder

Accessories

Clamping nut M14 Type NUT	073930 NUT
Clamping nut M14 Type FIXTEC	073930 FIXTEC