



## Clamping head smooth, SK 52, Clamping $\varnothing$ (0.5 mm increments): 7,5mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 329920 7,5    |
| GTIN         | 2050001074089 |
| Item class   | 33H           |

### Description

#### Version:

Smooth version for precision machining.

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify required clamping  $\varnothing$  with order.**

#### Application:

Versatile application range, machining centres, measuring machines or pallet clamping.

#### Note:

**Clamping heads for special profiles to your individual requirements on request.**

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

### Technical description

|                        |            |
|------------------------|------------|
| Clamping $\varnothing$ | 7.5 mm     |
| Profile                | round      |
| Clamping face          | smooth     |
| Clamping range         | 3 - 7.5 mm |
| Hardness               | 60 HR      |

|                 |                    |
|-----------------|--------------------|
| Length L        | 46 mm              |
| Version         | shortened fittings |
| Adapter         | SK 52              |
| Type of product | Clamping head      |