



**Clamping head with transverse serrations., SK 52, Clamping  $\varnothing$  (0.5 mm increments): 10 mm**



## Order data

Order number	329922 10
GTIN	2050001072146
Item class	33H

## Description

### Version:

With transverse serrations for raw material, small  $\varnothing$ .

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify required clamping  $\varnothing$  with order.**

### Application:

Versatile application range, machining centres, measuring machines or pallet clamping.

### Note:

**Clamping heads for special profiles to your individual requirements on request.**

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

## Technical description

Clamping $\varnothing$	10 mm
Profile	round
Hardness	60 HR
Clamping face	Transverse serrations

Clamping range	8 - 10.5 mm
Length L	46 mm
Adapter	SK 52
Type of product	Clamping head