



Clamping head smooth, SK 52, Clamping \varnothing (0.5 mm increments): 50,5mm



Order data

| | |
|--------------|---------------|
| Order number | 329920 50,5 |
| GTIN | 2050001074591 |
| Item class | 33H |

Description

Version:

Smooth version for precision machining.

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify required clamping \varnothing with order.**

Application:

Versatile application range, machining centres, measuring machines or pallet clamping.

Note:

Clamping heads for special profiles to your individual requirements on request.

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

Technical description

| | |
|------------------------|------------|
| Clamping \varnothing | 50.5 mm |
| Clamping face | smooth |
| Hardness | 60 HR |
| Profile | round |
| Clamping range | 3 - 7.5 mm |

| | |
|-----------------|--------------------|
| Length L | 46 mm |
| Version | shortened fittings |
| Adapter | SK 52 |
| Type of product | Clamping head |