



**Clamping head smooth, SK 52, Clamping  $\varnothing$  (0.5 mm increments): 51,5mm**



## Order data

Order number	329920 51,5
GTIN	2050001074614
Item class	33H

## Description

### Version:

Smooth version for precision machining.

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify required clamping  $\varnothing$  with order.**

### Application:

Versatile application range, machining centres, measuring machines or pallet clamping.

### Note:

**Clamping heads for special profiles to your individual requirements on request.**

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

## Technical description

Clamping $\varnothing$	51.5 mm
Clamping range	3 - 7.5 mm
Clamping face	smooth
Hardness	60 HR
Profile	round

Length L	46 mm
Version	shortened fittings
Adapter	SK 52
Type of product	Clamping head