



Clamping head smooth, SK 52, Clamping \varnothing (0.5 mm increments): 33mm



Order data

Order number	329920 33
GTIN	2050001072023
Item class	33H

Description

Version:

Smooth version for precision machining.

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify required clamping \varnothing with order.**

Application:

Versatile application range, machining centres, measuring machines or pallet clamping.

Note:

Clamping heads for special profiles to your individual requirements on request.

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

Technical description

Clamping \varnothing	33 mm
Clamping range	3 - 7.5 mm
Profile	round
Clamping face	smooth
Hardness	60 HR

Length L	46 mm
Version	shortened fittings
Adapter	SK 52
Type of product	Clamping head